



ADVANTEC

Carbon-Gewebe

| Type | Faser | Breite cm | Gewicht ca. g / m ² | Faden- Zahl | | Garn- feinheit in tex | | Dicke ca. mm | |
|-----------|-------|--------------|-----------------------------------|----------------|-------|-----------------------------|-------|-----------------|---------|
| | | | | Kette | Schuß | Kette | Schuß | Gewebe | Laminat |
| CVL-66/1 | C | 100 | 66 | 5 | 5 | 67 | 67 | 0,10 | 0,09 |
| CVL-80/1 | C | 100 | 80 | 6 | 6 | 67 | 67 | 0,11 | 0,10 |
| KDL-8023 | C | 120 | 95 | 7 | 7 | 70 | 70 | 0,15 | 0,12 |
| CVL-120/1 | C | 100 | 120 | 9 | 9 | 67 | 67 | 0,14 | 0,13 |
| KDL-8048 | C | 120 | 160 | 4 | 4 | 200 | 200 | 0,25 | 0,20 |
| KDL-8003 | C | 120 | 200 | 5 | 5 | 200 | 200 | 0,30 | 0,25 |
| KDK-8042 | C | 120 | 200 | 5 | 5 | 200 | 200 | 0,30 | 0,25 |
| KDK-8043 | C | 120 | 240 | 6 | 6 | 200 | 200 | 0,35 | 0,28 |
| KDK-8054 | C | 120 | 280 | 7 | 7 | 200 | 200 | 0,40 | 0,32 |
| KDL-8051 | C | 120 | 320 | 4 | 4 | 400 | 400 | 0,50 | 0,40 |
| KDL-8050 | C | 120 | 325 | 3 | 3 | 800 | 200 | 0,50 | 0,40 |
| KDK-8045 | C | 120 | 400 | 5 | 5 | 400 | 400 | 0,60 | 0,45 |
| KDL-8001 | C | 120 | 480 | 3 | 3 | 800 | 800 | 0,70 | 0,60 |
| KDK-8004 | C | 120 | 650 | 4 | 4 | 800 | 800 | 0,90 | 0,70 |
| MDL-9001 | C / G | 120 | 135 | 6 | 5 | 200 | 34G | 0,15 | 0,12 |
| MDL-9020 | C / G | 120 | 170 | 6 | 4 | 200 | 136G | 0,20 | 0,15 |
| PDL-9018 | C / A | 85 | 165 | 5 | 4 | 200C | 158A | 0,25 | 0,20 |
| | | | | | | 160A | 200C | | |
| PDK-9004 | C / A | 120 | 215 | 6 | 6 | 200C | 200C | 0,30 | 0,25 |
| | | | | | | 160A | 160A | | |
| KDL-5002 | C | 12 | 24 | 5 | 5 | 200 | 200 | 0,30 | 0,25 |
| MDL-6005 | C / G | 15 | 40 | 4 | 5 | 400C | 68G | 0,35 | 0,28 |
| | | | | | | 136G | | | |
| MDL-6007 | C / G | 36 | 70 | 3 | 6 | 800C | 68G | 0,35 | 0,28 |

C = Carbon xxL = Leinwand
 G = Glas xxK = Köper
 A = Aramid

