

ABB MC

LP
PILOTES
LOCATING PIN

CNOMO
DIN
NAAMS

LP

Pilote MABEC G... MABEC G... locating pin CNOMO – DIN



G866 241 223



G866 241 269




G866 241 295



G866 241 602



G866 241 604



LP : Locating Pin - Pilote					
N° Standard	D1= mm	D2= mm	H= mm	L= mm	W = Kg
G866 241 223	4,8	12	28	14	
G866 241 269	12	12	22	14	
G866 241 295	19,8	12	13	14	
G866 241 602	20,3	20	32	22	
G866 241 604	24,8	20	23	22	

Pilote MABEC R... MABEC R... Locating pin

CNOMO – DIN

1/4



R100 136 625



R100 136 627



R100 136 628



R100 136 629



R100 136 632



R100 136 633



R100 136 634



R100 136 635



R100 136 636




R100 136 637



R100 136 638



R100 136 639




LP : Locating Pin - Pilote				
N° Standard	A= mm	B= mm	L= mm	U= mm
R100 136 625	5	12	18	14
R100 136 627	5	12	28	14
R100 136 628	6	12	18	14
R100 136 629	6	12	28	14
R100 136 632	8	12	28	14
R100 136 633	8	12	38	14
R100 136 634	10	12	28	14
R100 136 635	10	12	38	14
R100 136 636	12	12	28	14
R100 136 637	12	12	38	14
R100 136 638	14,3	12	38	14
R100 136 639	14,3	12	48	14


Pilote MABEC R... MABEC R... Locating pin

CNOMO – DIN

2/4



R100 281 032



R100 282 998



R100 136 640




R100 136 641



R100 136 642




R100 136 644




R100 136 645




R100 136 646



R100 225 603



R100 225 605



LP : Locating Pin - Pilote				
N° Standard	A= mm	B= mm	L= mm	U= mm
R100 281 032	15,8	12	38	14
R100 282 998	15,8	12	48	14
R100 136 640	16,3	12	38	14
R100 136 641	16,3	12	48	14
R100 136 642	18,3	12	38	14
R100 136 644	18,3	12	48	14
R100 136 645	19,8	12	38	14
R100 136 646	19,8	12	48	14
R100 225 603	20,3	12	38	14
R100 225 605	20,3	12	48	14

Pilote MABEC R... MABEC R... Locating pin

CNOMO – DIN

3/4



R100 136 647



R100 136 648




R100 136 650




R100 136 651




R100 136 652



R100 136 653



R100 136 654



LP : Locating Pin - Pilote				
N° Standard	A= mm	B= mm	L= mm	U= mm
R100 136 647	24,3	20	48	22
R100 136 648	24,3	20	58	22
R100 136 650	29,8	20	58	22
R100 136 651	34,8	20	58	22
R100 136 652	39,8	30	58	22
R100 136 653	44,8	30	58	22
R100 136 654	49,8	30	58	22

Pilote d'écrous MABEC R...

MABEC R... Locating pin for nuts

CNOMO – DIN

4/4



R100 136 657



R100 136 658



R100 136 660



R100 136 661



R100 136 662




R100 136 664



R100 136 667



R100 136 668



LP : Locating Pin - Pilote				
N° Standard	A= mm	B= mm	L= mm	U= mm
R100 136 657	4,8	12	23	14
R100 136 658	4,8	12	33	14
R100 136 660	6,55	12	23	14
R100 136 661	6,55	12	33	14
R100 136 662	8,3	12	23	14
R100 136 664	8,3	12	33	14
R100 136 667	10,05	12	33	14
R100 136 668	10,05	12	33	14

LP

Pilote TOWER int. M6 TOWER locating pin int. M6 CNOMO – DIN



9928920



9928922




9928924



9928926



9928928



LP : Locating Pin - Pilote					
N° Standard	D1= mm	D2= mm	H= mm	L= mm	W = Kg
9928920	8	12	15	13	
9928922	10	12	15	13	
9928924	12	12	15	13	
9928926	16	12	15	13	
9928928	20	12	15	13	

LP

Pilote TOWER ext. M8 TOWER locating pin ext. M8 CNOMO – DIN



9928921



9928923




9928925



9928927



9928929



LP : Locating Pin - Pilote					
N° Standard	D1= mm	D2= mm	H= mm	L= mm	W = Kg
9928921	8	12	15	13	
9928923	10	12	15	13	
9928925	12	12	15	13	
9928927	16	12	15	13	
9928929	20	12	15	13	

LP Pilote Locating pin

NAAMS

1/2



APS063M



APS064M



APS083M



APS084M



APS103M



APS104M



APS133M




APS134M



APS163M



APS164M



LP : Locating Pin - Pilote					
Code NAAMS	D1= mm	D2= mm	A= mm	L= mm	W = Kg
APS063M	5,85	15,98	30	10	
APS064M	5,85	15,98	40	10	
APS083M	7,85	15,98	30	10	
APS084M	7,85	15,98	40	10	
APS103M	9,85	15,98	30	10	
APS104M	9,85	15,98	40	10	
APS133M	12,85	15,98	30	10	
APS134M	12,85	15,98	40	10	
APS163M	15,85	15,98	30	10	
APS164M	15,85	15,98	40	10	

LP Pilote Locating pin

NAAMS
2/2



APS193M




APS194M



APS253M



APS254M



LP : Locating Pin - Pilote					
Code NAAMS	D1= mm	D2= mm	A= mm	L= mm	W = Kg
APS193M	18,85	15,98	30	10	
APS194M	18,85	15,98	40	10	
APS253M	24,85	15,98	30	10	
APS254M	24,85	15,98	40	10	