

SERIES 69

CAST IRON SOLID WHEELS



Wheel description

Cast iron solid wheels.

Hub

The hub is available with plain bearing and with ball.

Diameters: 80-400 mm

Carrying capacity: 280-2800 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL

Max. carrying capacity 400 daN – available diameters 80-300 mm

Top plate fastening. Front-locking brake systems.



Medium-heavy duty brackets type P

Max. carrying capacity 750 daN – available diameters 80-200 mm

Top plate fastening. Front-locking and adjustable rear-locking brake systems



Extra-heavy duty brackets type EP

Max. carrying capacity 1600 daN – available diameters 100-250 mm

Top plate fastening. Adjustable rear-locking brake systems

Uses

Environments

Suitable for environments where medium-harsh chemicals are present; not suitable for applications in humid environments with strong acids or chlorinated solvents.

The wheel with plain bore is resistant to temperatures from -40 °C to +400 °C. To use the wheel+bracket assemblies at temperatures above 100°C, the wheel will have to be mounted with a special bracket.

Floors



Handling

